


EVA MS-DIN PLUS & MS-DIN / MS-R



Chamber of
EVA MS DIN/MS-R PLUS

FEATURES AND BENEFITS

- Temperature range -20°C to $+150^{\circ}\text{C}$ (according to model).
- Fast temperature regulation by Peltier element.
- Compatible with coaxial cylinders.
- Compatible with MS-R measuring system (according to model).

AVAILABLE TEMPERATURE DEVICES

Compatible only with bayonet coupling device

Designation	Ref.	Temperature range	Type	Bath*	Prog***	Compatible instrument	Compatible measuring system	Dimensions (p x l x h) in mm	Weight
EVA MS DIN PLUS	N950000	$+5^{\circ}\text{C}$ to $+65^{\circ}\text{C}$	Peltier	No	No	B-ONE FIRST RM100** RM200 DSR 500	MS DIN, MS SV, MS ULV, MS-Chocolat	610x340x650	15Kg
EVA MS DIN PLUS	N950005	$+5^{\circ}\text{C}$ to $+65^{\circ}\text{C}$	Peltier	No	Yes				
EVA MS DIN PLUS	N950003	-20°C to $+100^{\circ}\text{C}$	Peltier	Yes	No				
EVA MS DIN PLUS	N950012	-20°C to $+100^{\circ}\text{C}$	Peltier	Yes	Yes				
EVA MS DIN PLUS	N950008	0°C to $+150^{\circ}\text{C}$	Peltier	No	No				
EVA MS DIN PLUS	N950009	0°C to $+150^{\circ}\text{C}$	Peltier	No	Yes				
EVA 100 PLUS	N950100	Room T°C to $+100^{\circ}\text{C}$	Electrical	No	No	RM100** RM200 DSR 500	MS DIN, MS SV, MS ULV, MS-Chocolat, MS-R	610x340x650	15Kg
EVA MS DIN/MS-R PLUS	N950002	$+5^{\circ}\text{C}$ to $+65^{\circ}\text{C}$	Peltier	No	No				
EVA MS DIN/MS-R PLUS	N950004	$+5^{\circ}\text{C}$ to $+65^{\circ}\text{C}$	Peltier	No	Yes				
EVA MS DIN/MS-R PLUS	N950013	-20°C to $+100^{\circ}\text{C}$	Peltier	Yes	No				
EVA MS DIN/MS-R PLUS	N950020	-20°C to $+100^{\circ}\text{C}$	Peltier	Yes	Yes				
EVA MS DIN/MS-R PLUS	N950030	0°C to $+150^{\circ}\text{C}$	Peltier	No	No				
EVA MS DIN/MS-R PLUS	N950040	0°C to $+150^{\circ}\text{C}$	Peltier	No	Yes				

* Circulating bath not included. Required for counter cooling of Peltier. / ** Compatible with Portable RM100 and RM100 i. / *** Allow temperature setting by measuring head or RheoTex software.